




Architectural Rigging Systems  
 FULL SCALE DRAWING ATTACHED - UNITS = IMPERIAL


RONSTAN ARCHITECTURAL RIGGING SYSTEMS  
 45 HIGH POINT AVE., SUITE 2  
 PORTSMOUTH, RI 02871  
 PHONE: 401) 293-0539  
 FAX: (401)293-0538  
 www.ronstan.com/arch



- SELECT ROD DIAMETER
- M30 = 28 MM (ARS2-SSM30)
  - M36 = 34 MM (ARS2-SSM36)
  - M42 = 39 MM (ARS2-SSM42)
  - M48 = 45 MM (ARS2-SSM48)
  - M56 = 52 MM (ARS2-SSM56)
  - M64 = 69 MM (ARS2-SSM64)
  - M76 = 72 MM (ARS2-SSM76)
  - M85 = 82 MM (ARS2-SSM85)
  - M90 = 87 MM (ARS2-SSM90)
  - M100 = 97 MM (ARS2-SSM100)

**NOTES:**

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.
2. DO NOT SCALE DRAWINGS.
3. DRAWING FOR QUOTATION PURPOSES ONLY.
4. FOR ADDITIONAL INFORMATION CONTACT:  
 RONSTAN ARCHITECTURAL RIGGING SYSTEMS  
 45 HIGH POINT AVE., SUITE 2, PORTSMOUTH, RI 02871  
 TEL: (401) 293-0539 FAX: (401) 293-0538  
 WEBSITE: www.ronstan.com/arch  
 EMAIL: archcad@ronstan.us



**(ARS2-SSMxx) ROD ASSEMBLY SYSTEM DRAWING**

ADJUSTABLE LENGTH - 28 MM TO 97 MM DIA ROD, ADJUSTABLE FORK TERMINATION CLEVIS, STANDARD STAINLESS STEEL