




Architectural Rigging Systems
 FULL SCALE DRAWING ATTACHED - UNITS =IMPERIAL


RONSTAN ARCHITECTURAL RIGGING SYSTEMS
 45 HIGH POINT AVE., SUITE 2
 PORTSMOUTH, RI 02871
 PHONE: (401) 293-0539
 FAX: (401)293-0538
 www.ronstan.com/arch



- SELECT CABLE DIAMETER
- 19 - 04 = 1/8 INCH WIRE 1X19 (ABS3-19-04)
- 19 - 05 = 5/32 INCH WIRE 1X19 (ABS3-19-05)
- 19 - 06 = 3/16 INCH WIRE 1X19 (ABS3-19-06)
- 77 - 04 = 1/8 INCH WIRE 7X7 (ABS3-77-04)
- 77 - 05 = 5/32 INCH WIRE 7X7 (ABS3-77-05)
- 77 - 06 = 3/16 INCH WIRE 7X7 (ABS3-77-06)

NOTES:

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.
2. DO NOT SCALE DRAWINGS.
3. DRAWING FOR QUOTATION PURPOSES ONLY.
4. FOR ADDITIONAL INFORMATION CONTACT:
 RONSTAN ARCHITECTURAL RIGGING SYSTEMS
 45 HIGH POINT AVE., SUITE 2, PORTSMOUTH, RI 02871
 TEL: (401) 293-0539 FAX: (401) 293-0538
 WEBSITE: www.ronstan.com/arch
 EMAIL: archcad@ronstan.us



(ABS3-xx-xx) CABLE ASSEMBLIES

MICROLOC TAMPER RESISTANT TURNBUCKLE RAILING INFILL 1/8 INCH, 5/32 INCH & 3/16 INCH DIA. WIRE