

TYPICAL
JAMB STUD
OR POST

WHERE BRACING TERMINATES
AT BUILT-UP JAMB OR POST,
EXTEND CHANNEL INTO PUNCH-OUT.
USE 2"x2"x16 GAUGE CLIP ANGLE
1-1/4" LESS THAN STUD WIDTH.
ATTACH USING (4)#10-16 SCREWS.

150U50-54 COLD ROLLED CHANNEL.
(1-1/2"x16 GAUGE CRC)
TO BE SPACED AS REQ'D
BY DESIGN.

TYP. WALL STUD

2"x2"x16 GAUGE CLIP ANGLE
1/4" LESS THAN STUD WIDTH. ATTACH
USING (4)#10-16 SCREWS.
PLACE CLIP ANGLE AT EACH STUD.

TYP. LATERAL BRACING SPLICE USE:
(1)12" LONG CRC INVERTED OVER
CENTER OF SPLICE w/(3)#10-16
SCREWS ON EACH SIDE OF SPLICE.

THIS DETAIL IS NOT RECOMMENDED
FOR WALL STUDS DEEPER THAN 8"



CLARKWESTERN
DESIGN

East Coast - Atlanta, GA
20 Mansell Court East, Suite 350B
Roswell, GA 30076

West Coast - San Diego, CA
2035 Corte Del Nogal, Suite 165
Carlsbad, CA 92011

Toll Free Phone: 877-832-3206

CRC LATERAL BRACING

LOAD BEARING & NON-LOAD BEARING
3 5/8" THRU 8" STUDS